

**STANLEY**  
**FATMAX**



## STANLEY® FATMAX® XTREME™ 8M (32MM WIDE) TAPE MEASURE FMHT38217-0

**XTREME™** Tape for extreme jobs. Introducing the **STANLEY® FATMAX® XTREME™ 8M (32MM WIDE) TAPE MEASURE**: the single answer to all your measuring needs. This heavy-duty tape is engineered for a multitude of professional applications, delivering precise measuring performance.

- **FINGER BRAKE FOR ULTIMATE BLADE CONTROL:** Equipped with an integrated finger brake for improved blade retracting control and ergonomics.
- **DOUBLE-SIDED PRINT:** Clear double-sided print ensures high visibility and precise vertical and overhead measuring.
- **OVERSIZED BEAST HOOK:** The robust, oversized Beast Hook ensures excellent material grab.
- **5 METRE MAXIMUM REACH:** Long, straight and strong reach enables efficient measuring when working alone.
- **ONE TAPE FOR ALL YOUR MEASURING NEEDS:** versatile, heavy-duty professional tape engineered for professional applications.
- **PRECISE MEASUREMENT:** Delivers precise measuring performance with ultimate control.
- **16CM BLADEARMOR® COATING:** Delivers optimum hook connection, strength and resilience against abrasion and wear.
- **RANGE OF LENGTHS:** Available in 5M, 8M and 10M lengths.



**THE MEASURE OF A PRO™**  
[STANLEYTOOLS.COM](http://STANLEYTOOLS.COM)