



LED/Multiled	LED	Optimum voltage (V)	220Vac	Intensity	2800mcd@20mA
Mounting Size	14mm	Rectifier	Half Wave		
Mounting Finish	Chrome Bezel	AC current	3mA(max)		
Protection	IP67	DC current			
Mount Holder	Flush	Voltage Tolerance (%)	10%		
Chip Qty	1	Optimum temperature (°C)	-40°C...+85°C		
Indicator colour	Red	Storage temperature (°C)			
Wavelength (nm)	625	Contact Tab x 2	22AWG wire		



Dimension in mm (typical), not to scale.

We reserve the right to make changes without further notice to this product to improve reliability, function or design.