

# TT-11-30-0-L-EU



CABLE TIE 133NT 281MM BLK NYL TWIST



## General Information

Extended Product Type	TT-11-30-0-L-EU
Product ID	7TAG054780R0009
EAN	5414363925682
Catalog Description	CABLE TIE 133NT 281MM BLK NYL TWIST
Long Description	Twist Tail Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 281mm (11.1 Inches), Width of 4.7mm (0.186 Inch), Thickness of 1.37mm (0.054 Inch), Tensile Strength Rating of 133 Newtons (30 Pounds), Maximum Bundle Diameter 76.2mm (3.0 Inches), 50 Pack
Lock Type	Plastic Pawl

## Ordering

EAN	5414363925682
Minimum Order Quantity	1000 piece
Customs Tariff Number	3926909990

## Dimensions

Product Net Weight	2.223 g
--------------------	---------

## Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	127 mm
Package Level 1 Height	12.7 mm
Package Level 1 Depth / Length	381 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	203.2 mm
Package Level 2 Height	174.498 mm
Package Level 2 Depth / Length	409.448 mm
Package Level 2 EAN	50728494145889

## Additional Information

Brand / Label	Catamount
Color	Black

Function	Bend again and twist motion.™
Material	Nylon/Polyamide 6.6
Order Multiple	1000 piece
Product Main Type	CABLE TIES AND ACCESSORIES
Product Name	PLASTIC CABLE TIE
Product Type	Twist Tail
Special Functions	Designed for quick, easy, tool-less installation. After installing, remove excess tail with a simple bend
UPC	728494145884

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TT-11-30-0-L-EU
Instructions and Manuals	TT-11-30-0-L-EU

---

### Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

---

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

