



R-266

Insulated waterproof impact gloves, ensuring warm, dry heavy-duty hand protection



Impact



Cold

Abrasion Protection



Cut



Heavy Duty

Insulated waterproof impact gloves, ensuring warm, dry heavy-duty hand protection

- **Specialized protection:** RINGERS® R266 work gloves' patented TPR (thermoplastic rubber) design, developed with F3 Technology™, ensures knuckles, thumb and finger-length impact protection
- **Strengthened grip:** A Kevlar®-stitched synthetic leather palm, with a special grip patch system, offers excellent grip in varying conditions
- **Added defenses:** These RINGERS® gloves also feature 100g Thinsulate™ insulation and a proprietary waterproof barrier, for warm, dry hand protection in harsh environments
- **Enhanced features:** Touchscreen-compatible thumb tips, index and middle fingers limit glove removals, for safer technological interaction, while an extended neoprene TPR pull tab wrist closure and increased visibility surface design further enhance workplace safety



Industries

- Mining
- Oil and gas

Applications

- Engagement and release of drill string slips
- Chaining up pipes
- Installation and dismantling of rigs
- Assembly and disassembly of large pipes
- Unloading and stacking pipe
- Preparation of site - unloading of lines and valves
- Set-up of pressure manifold and tubing injector head
- General pumping work
- Preparation of site - set-up and disassembly of tool string
- Handling iron - rigging work
- Handling of tools
- Environmental clean-up and remediation
- Handling iron
- Valve - line maintenance and repair
- Heavy machine operation
- Equipment maintenance and repair
- Pipe handling



R-266

Insulated waterproof impact gloves, ensuring warm, dry heavy-duty hand protection

Key Features

- **Patented TPR design:** Knuckles, thumb and finger-length impact protection
- **Synthetic leather grip patch system:** Secure all-weather grip
- **Waterproof barrier and 100g Thinsulate™ insulation:** Warm, dry hands

Performance Standards & Regulatory Compliance

ANSI/ISEA 138-2019



ANSI/ISEA 105-2024



EN388: 2016



3233BP

EN 511



221

Technologies



Touchscreen Compatible

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R266	Liner Material: Polyester Cuff Style: Extended		8, 9, 10, 11, 12, 13	Black and Red	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

