221 Series

Compact Lever Connectors



Technical Data

solid & stranded 0.2 - 4mm² 0,14 - 4mm² fine-stranded 450 V/4 kV/20 32 A

____ 11 mm

Description.	ltem No.	Box Unit.
transparent housing		
O 2-conductor	221-412	100
3-conductor	221-413	50
O =	224 445	٥٢

221 Series - 6mm ²		
Accessories		
Mounting Carrier	221-510	10
Strain Relief Plate	222-505	10

solid, stranded &

221-612

221-613

221-615

50

30

15

fine-stranded

Technical Data

450 V/4 kV/20

____ 13 mm

transparent housing O 2-conductor

3-conductor

○ 5-conductor

0.5 - 6mm²

41 A

O 5-conductor	221-415
In grounded (earthe	d) supply systems

221 Series - 4mm ²		
Accessories		
Mounting Carrier	221-500	10
Strain Relief Plate	222-505	10
Angled DIN-rail adapter	222-510	10
Carriers for screw mo	unting	
O 2-conductor	221-502	10
3-conductor	221-503	10
○5-conductor	221-505	10

For all options please contact us.


NEW 6mm² version








Operating



1. Strip the conductor 11mm (4mm² version) or 13mm (6mm² version).



2. Open clamping unit using the lever and insert the conductor.




3. Lower the lever to close the clamp to complete the connection.4. To remove, lift the lever and pull out the conductor.

Advantages & Accessories




100% Transparent HousingSafety check

- Wire inserted properly
- Insulation stripped properly



Two test slots
Front and back of the housing

Easy testing while installed



WAGOBOX XL Part No. 60339091 (PU1)

- Suitable for the 221 (4mm² version only) and 2273 series
- Can be used within maintenance free applications



NEW Mounting Carriers



 Screw or snap-in mounted carriers for horziontal or vertical mounting for the 4mm² version only.