

## FEATURES

- **Sintered Bronze Material:** Provides high strength and excellent wear resistance, ensuring long-lasting performance.
- **12 mm Length:** Suitable for compact installations where space is limited.
- **16.04 mm Outer Diameter:** Ensures compatibility with a wide range of housings and applications.
- **11.98 mm Shaft Diameter:** Designed for precise fit and optimal performance with standard shafts.
- **Low Friction:** Reduces energy consumption and enhances efficiency in mechanical systems.
- **Self-lubricating:** Minimises maintenance requirements and extends service life.

**RS PRO 12 mm Sintered Bronze Plain Bearing, 16.04 mm Outer Diameter**

RS Stock No: 528-291



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO plain bearing is designed for applications requiring low friction and high wear resistance. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. The bearing is ideal for supporting rotating or sliding shafts, ensuring smooth and efficient operation.

## General Specifications

Product Type	Plain Bearing
Shaft Diameter	11.98 mm

## Mechanical Specifications

Length	12 mm
Material	Sintered Bronze
Outside Diameter	16.04 mm

