

IS-3 Standard ; 0 ... 2.5 bar; 4...20 mA, 2-wire

IS-3 Standard ; 0 ... 2.5 bar; 4...20 mA, 2-wire

Item number:	46879357
Quantity:	1 pcs.
Order code:	IS-3-0-2111-1ZZ-BBFHDLZ-GTA3ZZZ-UAZZ 5W101AIS3ZZSF2ASQOGSI3
Overview:	IS-3 Standard ; 0 ... 2.5 bar; 4...20 mA, 2-wire @ 10 ... 30 V DC Accuracy: 0.5% of span G 1/4 A DIN EN ISO 1179-2 Sealing: FPM/FKM Wetted parts: stainless steel Adjustability: Zero/span adjustable angular connector acc. to DIN EN 175301-803 A PG9 Cable material: without Cable length: without U+=1, U-=2 permitted media temperature: -20...+80°C Approvals: ATEX/IECEX II 1/2G Ex ia IIC T4/T5/T6 Ga/Gb Additional certifications: without Special features: without Test protocol: without test protocol Additional ordering information: without Specifications according to data sheet: PE 81.58
Details:	IS-3 Standard ; 0 ... 2.5 bar; 4...20 mA, 2-wire @ 10 ... 30 V DC Accuracy: 0.5% of span G 1/4 A DIN EN ISO 1179-2 Sealing: FPM/FKM Wetted parts: stainless steel Adjustability: Zero/span adjustable angular connector acc. to DIN EN 175301-803 A PG9 Cable material: without Cable length: without U+=1, U-=2 permitted media temperature: -20...+80°C Approvals: ATEX/IECEX II 1/2G Ex ia IIC T4/T5/T6 Ga/Gb Additional certifications: without Special features: without Test protocol: without test protocol Additional ordering information: without

Date: 22/01/2024



Specifications according to data sheet: PE 81.58