

Datasheet

Stock No: 178-5731

RS Pro Thermal Line Panel Printer – High Speed



Specification	
Print Method	Thermal Line
Print Speed	30mm/s
Resolution	8 dots/mm, 384 dots/line
Effective Printing Width	48mm
Character Set	ASCII, GB18030(Chinese), BIG5, Codepage
Print Font	Font A: 12x24 Font B: 8x16
Paper Type	Thermal Paper
Paper Width	57.5± 0.5mm
Paper Thickness	0.06~0.08mm
Paper Roll Diameter	Max: 40.0mm
Roll Core Inner Diameter	13mm(min.)
MCBF Reliability	5million lines
Barcode	UPC-A, UPC-E, EAN-13, EAN-8, CODE39, ITF25, CODEBAR, CODE93, CODE128
Emulation	ESC/POS
Driver	Windows98/2000/NT/XP/Vista/Win7/Win8
Interface	RS-232/Parallel
Paper Supply Method	Drop-in easy paper loading
Power Supply (Adapter)	RS232: DC3.5V-8.5V, 3A; Parallel: DC5V-8V, 3A
Outline Dimension (WxDxH)	110x64x57mm
Installation Port Size	103x57x51mm
Weight	200g
Operating Temp	0 ~ 50 °C
Operating Humidity	20 ~ 80%

ENGLISH