



REV	DESCRIPTION	DATE
-----	-------------	------

NOTE:

1. MAXIMUM ELECTRIC CURRENT:  

A.W.G.	12	10
AMP.	35	50
2. MAXIMUM ELECTRICAL RATING:  
75°C 600 VOLTS MAX.
3. INSULATION MATERIAL: VINYL
4. INSULATION COLOR: YELLOW
5. TERMINAL MATERIAL: COPPER
6. WIRE RANGE: 12-10A.W.G. (4-6mm<sup>2</sup>)

Tolerance Unless Otherwise Specified	
0 >	mm ± ANGLE
>	mm ± 0° REF ±
>	mm ± ° ±
>	mm ± ° ±

NAME	NYLON-INSULATED SPADE TERMINALS			UNIT	mm	
PART NO.	SVYS5-6@	MATERIAL		APPROVE		
NUMBER	TZV-380	SCALE	SHEET	PAGE	CHECKED	
DATE	09/07/2005	3 : 1	1-0	1 OF 1	DRAWN	