

6 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

Product ID: DVIIDMM6



The DVIIDMM6 6ft DVI-I Dual Link cable features 2 male DVI-I (29-pin) connectors and provides a reliable connection between your desktop or laptop computer and a DVI-I monitor or projector.

The 6ft DVI-I male to male cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-I Dual Link display or projector

Features

- Ondersteunt een maximale resolutie van 1920x1200
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrietkern elimineert EMI-interferentie
- Aluminum-Mylar folie met gevlochten afscherming
- Ondersteunt hot-plugging van DVI-beeldschermen
- Voldoet aan de DVI DDWG-specificaties
- Supports both analog and digital displays

Hardware	Warranty	Lifetime
	Connectormateriaal	Nikkel
	Industriestandaarden	DVI DDWG Standard
	Kabelafscherming	Aluminium-Mylar folie met vlechtwerk
	Type kabelmantel	PVC - Polyvinyl Chloride
Prestaties	Maximale overdrachtsnelheid	9.9 Gbits/sec
Connector(en)	Connector A	1 - DVI-I (29-polig) Mannelijk
	Connector B	1 - DVI-I (29-polig) Mannelijk
Fysieke eigenschappen	Draaddikte	28 AWG
	Gewicht product	10.9 oz [308 g]
	Kabellengte	6 ft [1.8 m]
	Kleur	Zwart
	Lengte product	6 ft [1.8 m]
Verpakkingsinformatie	Verzendgewicht (verpakt)	11.2 oz [318 g]
Wat wordt er meegeleverd	Meegeleverd	1 - 6 ft DVI-I Dual Link Digital Analog Monitor Cable M/M

Product appearance and specifications are subject to change without notice.