


RAD-PIG-EF316-MCX-N

Order No.: 2867681



Adapter cable, pigtail 50 cm MCX (male) -> N (male), insertion
attenuation 1.5 dB@2.4 GHz; impedance 50 Ω;

Commercial data

EAN	 4 017918 939052
Pack	1
Customs tariff	85442000
Gross weight in pieces	42.80 g
Country of Origin	PL
Catalog page information	Page 653 (IF-2011)

Product notes

WEEE/RoHS-compliant since:
01/10/2005



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General**

Connection 1	Plug connector connection
Connection method	MCX (male)
Connection 2	Plug connector connection
Connection method	N (male)
Fixed cable length	50 cm
Cable type	EF 316

Cable, attenuation	approx. 1.5 dB/m
	approx. 0.83 dB/m for 900 MHz
	approx. 1.27 dB/m for 1.8 GHz
	approx. 1.52 dB/m for 2.4 GHz
	approx. 2.48 dB/m for 5 GHz
Minimum bending radius	12.50 mm
External diameter	2.50 mm
Outer sheath, material	RADOX®(LSFH)
Connection name	Plug connector connection
Connection method	MCX (male)
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Certificates

Certification

Certifications applied for:

Certification Ex:

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;