

Cut-off Saw LXT®

DLW140

18V X2 • 355 mm • 3 800 min⁻¹

Cut-off saw for safe, spark-free metal cutting

A powerful cut-off saw for accurate, safe and quick cutting of metal. A high 36V is achieved with two 18V LXT® batteries. A carry handle for easy transport and a spark guide for added safety. An adjustable cutting depth and material clamp improve user convenience.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	3800 min ⁻¹
Max. Log Diameter	127 mm
Capacity 90°	119 x 119 mm
Capacity 45°	106 x 106 mm
Max. Cutting Capacity in Steel Pipe	127 mm
Max Cutting Capacity	102 x 194 mm
Bore Size (Arbor Diameter)	25,4 mm
Disc Diameter	355 mm
Sound Power Level (L _{WA})	115 dB(A)
Sound Pressure Level (L _{pA})	103 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)

User benefits

- Quick release vise ensures secure fastening and quick repeated cut-offs.
- Electric brake for maximum productivity and increased operator safety
- Brushless motor provides high power and excellent cutting performance
- Soft start for smooth start-ups
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

■ **Optional AC**

B-64696-5

Cut - off wheel 355 x 2,5 x 25,4 mm,



■ **Other**

User manual

Parts drawing