

FIG 1 TEM-110-02-03.0-XX-D SHOWN

TABLE 1 "B" STACK HEIGHT "A" "C" "D" 5.375 [.2116] 5.610 [.2209] 5.742 [.2261] 2.200 [.0866] -03.0 -04.0 6.375 [.2510] 6.610 [.2602] 6.742 [.2654] 3.200 [.1260] -07.0 9.375 [.3690] 9.610 [.3783] | 9.742 [.2835] | 6.200 [.2441] PROPRIETARY NOTE

REPRESENTS A CRITICAL DIMENSION.

2. MINIMUM PUSHOUT FORCE FOR TERMINAL, LOCKING CLIP AND WELD TAB: 2.22N [0.50LBF]. 3. MAXIMUM POST HEIGHT VARIATION BETWEEN ANY TWO PINS: 0.13 [.005]

5. MAXIMON TO STITLIGHT VARIATION BETWELT ANT TWO TINS, 0.13 LOC 4. TEM PARTS TO BE PACKAGED IN TRAYS UNLESS OTHERWISE SPECIFIED. 5. POSITIONS -05 THRU -20 WILL HAVE ONLY ONE SLOT PER SIDE. POSITIONS -25 THRU -40 WILL HAVE TWO SLOTS PER SIDE.

POSITIONS -45 THRU -50 WILL HAVE THREE SLOTS PER SIDE.

6. SLOTS ONLY AVAILABLE IN -03.0 LEAD STYLE.

7. TEMS-TR ONLY FOR QUANTITIES UP TO 49 PIECES, NO LEADER, TRAILER, OR REEL WILL BE SUPPLIED. FOR QUANTITIES 50-124, NO LEADER, OR TRAILER WILL BE SUPPLIED

8. ALL SAMPLES AND/OR NO CHARGE ORDERS ARE REQUIRED TO BE PACKAGED IN SUSPENSION PACKS AND NOT T&R.

F:\DWG\MISC\MKTG\TEMX-1XX-XX-XX.X-XX-D-XX-XX-MKT.SLDDRW

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: **DECIMALS ANGLES**

X.X: ±0.3 [.01] X.XX: ±0.13 [.005] X.XXX: ±0.051 [.0020] THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN. MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART. TO ANY LINAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS

WRITTEN CONSENT OF SAMTEC, INC. SHEET SCALE: 4:1

DO NOT SCALE DRAWING

INSULATOR: LCP, COLOR: BLACK -L OPTION ONLY: LCP, COLOR: NATURAL

TERMINAL AND LOCKING CLIP: PHOS BRONZE 510 WELD TAB: BRASS ALLOY 260, FULL HARD




520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com


DESCRIPTION


0.8 mm TIGER EYE MICRO TERMINAL

TEMX-1XX-XX-XX.X-XX-D-XX-XX

BY: BRAY 10/18/2007 | SHEET 1 OF 3







PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMITE, CH. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATE IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENTO F SAMITE, IN

DO NOT SCALE DRAWING

SHEET SCALE: 4:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DESCRIPTION:

0.8mm TIGER EYE MICRO TERMINAL

DWG NO

TEMX-1XX-XX-XX,X-XX-D-XX-XX
BY: B RAY 10/18/2007 SHEET 3 OF 3