

STYLEA

5920UOI035P41-38x38/10 LOW

EAN 4031582409857



BETTER MOBILITY. BETTER LIFE.

Swivel castor, housing made of Polyamide, plate fitting. Wheel centre made of Polyamide, plain bearing



Picture may differ from original product

Technical Data

Wheel diameter	35 mm
Wheel width	11 mm
Castor width	52 mm
Size of Plate	38 x 38 mm
Plate hole centres	28 x 28 mm
Plate hole	5 mm
Offset	12 mm
Swivel Interference	74 mm
Overall height	41 mm
Temperature	- 10 / + 40 °C
Standard	EN_12528
Weight	0.08 kg
Swivel Radius	37 mm
Load capacity	50 kg
Load capacity (static)	100 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○