

ELECTRONIC SERVICE TOOL-SETS



special service sets for the maintenance and repairing of mobile phones and other high sensitive IT-Instruments. The tools are clearly arranged in cases made from dissipative black imitation leather, with zip fastener. 2251 Case with zip fastener, without tools, Outside dimensions: 190 x 135 x 35 mm (when closed)



CARAT

2250 BERNSTEIN[®] Carat

9-piece set dissipative tools from the series EUROline-Conductive to meet highest quality standards.

Weight: 0.360 kg

No.	Description of individual tools	No.	Description of individual tools
3-672-15	End cutters EUROline-Conductive, 130 mm, flush, for soft wire up to 0.8 mmØ cutting edge 20° angular, box joint, double leaf spring, fine polished and bright burnished, dissipative bicoloured hand guard	4-621	Cross-recess screwdriver size 000, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip
3-683-15	Snipe nose pliers EUROline-Conductive, 130 mm, plain jaws, box joint, double leaf spring, fine polished and bright burnished, dissipative bicoloured hand guard	4-623	Cross-recess screwdriver size 0, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip
4-601	Slotted screwdriver with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip, 50 x 0.8 mm	5-191	Tweezers, made from conductive and acid-resistant black plastic material, reinforced with glassfibre, 120 mm, with straight, rounded tips
4-603	Slotted screwdriver with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip, 50 x 1.5 mm	6-661	TORX-screwdriver T 5, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip
		6-663 L	TORX-screwdriver T 7, with bore-hole in the tip, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip