

FEATURES

- 6W LED
- 3.6V 1.8A Ni-Cd battery
- 200lm (DC)
- Polycarbonate base and cover
- Supplied with a pack of four self-adhesive legends
- IP65
- 3-hour minimum emergency duration
- Can be wired for maintained or non-maintained operation
- Constant light output when operating on mains or battery power

LED Emergency Lighting Bulkhead 6 W

RS Stock No.: 795-9735



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This IP65 rated LED bulkhead is a 3 hour maintained emergency light fitting. This LED emergency bulkhead offers an energy saving and cost effective solution to fulfil emergency lighting requirements. The bulkhead features a polycarbonate base and cover, with a steel gear tray. This emergency bulkhead is supplied with a set of four self-adhesive legends.

General Specifications

Lamp Type	LED
Light Style	Bulkhead
Luminosity	200lm
Maintained	Maintained
Legend	Virgo is supplied complete with a pack of four self-adhesive legends
Material	Polycarbonate
Finish	White
Duration	3h
Lamp Supplied	Yes
Applications	LED emergency exit signs are ideal for commercial, industrial and retail applications and can be found in: Corridors, Workshops, Emergency exits

Electrical Specifications

Wattage	6W
Voltage Rating	230V
Battery	3.6V 1.8A Ni-Cd

Mechanical Specifications

Length	352mm
Width	117mm
Depth	76mm
Fitting Type	Bulkhead
Gear Tray	Steel gear tray

Protection Category

IP Rating	IP65
-----------	------

Approvals

Compliance/Certifications	RoHS
---------------------------	------





795-9710	8W Emergency IP65 bulkhead maintained 3Hr
795-9722	Drop down attachment with set of legends

PRODUCT CODE	DESCRIPTION
795-9735	Maintained LED emergency IP65 Bulkhead 3Hr
795-9738	Non-Maintained LED emergency IP65 Bulkhead 3Hr

