

\* EKDMGN05-KIT  
 INDUCTOR  
 LQP03TN\_02/LQW15AN\_80/\_00

No.	P/N	QTY
1	LQP03TN0N6B02	10
2	LQP03TN0N7B02	10
3	LQP03TN0N8B02	10
4	LQP03TN0N9B02	10
5	LQP03TN1N0B02	10
6	LQP03TN1N1B02	10
7	LQP03TN1N2B02	10
8	LQP03TN1N3B02	10
9	LQP03TN1N5B02	10
10	LQP03TN1N6B02	10
11	LQP03TN1N8B02	10
12	LQP03TN1N9B02	10
13	LQP03TN2N0B02	10
14	LQP03TN2N2B02	10
15	LQP03TN2N3B02	10
16	LQP03TN2N4B02	10
17	LQP03TN2N7B02	10
18	LQP03TN3N0B02	10
19	LQP03TN3N3B02	10
20	LQP03TN3N6B02	10
21	LQP03TN3N9B02	10
22	LQP03TN4N0B02	10
23	LQP03TN4N3H02	10
24	LQP03TN4N7H02	10
25	LQP03TN5N1H02	10
26	LQP03TN5N6H02	10
27	LQP03TN6N2H02	10
28	LQP03TN6N8H02	10
29	LQP03TN7N5H02	10
30	LQP03TN8N2H02	10
31	LQP03TN9N1H02	10
32	LQP03TN10NH02	10
33	LQP03TN15NH02	10
34	LQP03TN22NH02	10
35	LQP03TN33NH02	10
36	LQP03TN47NH02	10
37	LQP03TN68NH02	10
38	LQP03TNR10H02	10
39	LQP03TNR22H02	10
40	LQP03TNR27H02	10
41	LQW15AN1N3C80	10
42	LQW15AN1N5C80	10
43	LQW15AN1N6C80	10
44	LQW15AN1N7C80	10
45	LQW15AN2N2B80	10
46	LQW15AN2N3B80	10
47	LQW15AN2N4B80	10
48	LQW15AN2N5B80	10
49	LQW15AN3N0B80	10
50	LQW15AN3N3B80	10
51	LQW15AN3N9B80	10
52	LQW15AN4N7B80	10
53	LQW15AN5N6B80	10
54	LQW15AN6N8G80	10
55	LQW15AN8N2G80	10
56	LQW15AN10NG80	10
57	LQW15AN11NG80	10
58	LQW15AN12NG80	10
59	LQW15AN15NG80	10
60	LQW15AN22NG80	10
61	LQW15AN27NG80	10
62	LQW15AN33NG80	10
63	LQW15AN39NG80	10
64	LQW15AN47NG80	10
65	LQW15AN56NG80	10
66	LQW15AN68NG80	10
67	LQW15AN75NG80	10
68	LQW15ANR10J00	10
69	LQW15ANR12J00	10