

FEATURES

- **60W power rating:** Delivers consistent heat for effective soldering
- **480°C maximum temperature:** Allows for a wide range of soldering applications
- **Dual plug type compatibility:** Supports Type G and Type E plugs for versatile use
- **Single output:** Simplifies operation with focused functionality
- **Compliance with standards:** Meets ANSI-ESD S20.20:2021, CE, REACH, RoHS, UKCA for safety and reliability

RS PRO 60W Soldering Station, 480°C Temperature

RS Stock No: 631-072



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 60W Soldering Station is designed for precision soldering tasks, providing reliable performance for both professional and hobbyist applications. With a maximum temperature of 480°C, it ensures efficient soldering of various components, making it ideal for electronics assembly and repair.

General Specifications

Number of Outputs	1
Product Type	Soldering Station
Soldering Tip Temperature	480 °C
Tasks Supported	Soldering

Protection Category

ESD Safe	No
----------	----

Electrical Specifications

Input Voltage	110-230 V
Plug Type	Type G - British 3-Pin, Type E - France-2 Round Pin
Power Rating	60 W

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, CE, REACH, RoHS, UKCA
---------------------	---

