

Ex enclosures Stainless steel, empty enclosure with hinged door – KEL 9401.600



Product description

Applications:

- Zone 1 and 2 or 21 and 22 to 94/9/EC
- Ambient temperature range: -30°C...+80°C
- Protection type to EN 60 079: Equipment protection thanks to increased safety, equipment protection thanks to enclosure

Material:

- Enclosure: Stainless steel 1.4301 (AISI 304)
- Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal
- Mounting plate: Sheet steel

Surface finish:

- Enclosure: Brushed, grain 240
- Mounting plate: Zinc-plated

Protection category IP to IEC 60 529:

- IP 66

Certificates:

- IEC Ex PTB 09.0035U: yes
- PTB 02 ATEX 1082U: yes

Supply includes:

- Enclosure
- Door
- Mounting plate

Packs of:

- 1 pc(s).

EAN:

- 4028177138681

**Customs tariff
number:**

- 94032080

Product features

Dimensions:

- Width: 200 mm
- Height: 300 mm
- Depth: 155 mm

Mounting plate:

- Width: 162 mm
- Height: 275 mm

Number of cam locks:



- 1

Weight:


- 3.8 kg

Approvals

Certificates:


-  [Ex \(EN\)](#)
-  [Ex \(DE\)](#)

Declarations:

-  [Manufacturer's declaration \(EN, DE\)](#)

Downloads

Documentation:

-  [Instructions \(EN, DE\)](#)