

FEATURES

- **Rubber Bush Design:** Provides excellent vibration isolation and noise reduction
- **10 mm Bore Size:** Ensures compatibility with a wide range of equipment
- **Compression Deflection of 11.25 mm:** Allows for effective absorption of vibrations
- **Compression Load of 1235 N:** Capable of handling substantial loads
- **Natural Rubber Material:** Offers durability and flexibility
- **Operating Temperature Range of -40 °C to 80 °C:** Suitable for various environmental conditions
- **Threaded Hole Mount Type:** Facilitates easy installation
- **Shore Hardness of Shore A 55:** Balances softness and durability

RS PRO Rubber Bush Anti-Vibration Mount, 10 mm Bore

RS Stock No: 714-174



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO anti-vibration mount is designed to reduce noise and vibration in machinery and equipment. With a 10 mm bore and robust construction, it is ideal for applications requiring reliable vibration isolation, enhancing equipment longevity and performance.

General Specifications

Anti Vibration Mount Type	Rubber Bush
Bore Length	10 mm
Bore Size	10 mm
Compression Deflection	11.25 mm
Compression Load	1235 N
Foot Colour	Black
Foot Height	45 mm
Foot Shape	Bobbin Shaped
Mount Type	Threaded Hole
Product Type	Anti-Vibration Mount
Shore Hardness	Shore A 55
Thread Size	M10

Mechanical Specifications

Material	Natural Rubber
Outside Diameter	57 mm
Overall Height	45 mm

Operation Environment Specifications

Maximum Operating Temperature	80 °C
Minimum Operating Temperature	-40 °C

Approvals

Standards/Approvals	RoHS
---------------------	------