



PRODUCT DATASHEET

Datasheet creation date: 2025/07/08 2:21 (UTC)



6205DDU

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	25	mm	Bore diameter
D	52	mm	Outside diameter
B	15	mm	Width
r (min.)	1	mm	Chamfer dimension

Basic Load Ratings

Cr	15400	N	Basic dynamic load rating
C0r	7850	N	Basic static load rating

Speeds

Grease	9000	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	30	mm	Diameter of shaft abutment
da (max.)	32	mm	Diameter of shaft abutment
Da (max.)	47	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet

Calculation factors

fo	13.9		Factor
----	------	--	--------

Additional information

z	9		Number of Balls
Dw	7.938	mm	Ball Diameter

Mass

Mass approx.	0.129	kg	Mass approx.
--------------	-------	----	--------------

