

133 75

Open ended slogging spanner

| | |
|-----------------------|--------------------|
| Code | ETIM |
| 6401230 | EC002130 |
| EAN | UNSPSC |
| 4010886640128 | 27-11-17-06 |
| Country of origin | eCl@ss |
| Germany | 21-04-01-02 |
| Customs tariff number | |
| 82041100 | |



Article description

- Design according to DIN 133
- Up to length 500 mm made of chrome vanadium steel 31CrV3, from length 525 mm made of material C35
- For heavy-duty work
- Special sizes available on request up to 250 mm
- * not standardised

Article information

| | | | |
|--------------------------|---------|---------------------------|-----------------|
| Contents [Qty of pieces] | 1 | Standard | DIN 133 |
| Net weight [kg] | 5,11 kg | Width across flats 1 [mm] | 75 |
| Total length [mm] | 390 mm | Head height 1 [mm] | 31 mm |
| Surface | oiled | Width of head 1 [mm] | 161,5 mm |
| Material | 31CrV3 | | |