

BCC M454-0000-2A-RM020-005

Order Code: BCC099A







C € [H[⊠

_				
P 2	CIC	tο	211	ires
$\Box a$	216	100	au.	11 53

Approval/Conformity

CE EAC

WEEE

Electrical connection

Conductor cross-section

Connection M12x1-Male, Straight, 4-pin, A-

coded

250 VDC / 250 VAC

0.25 mm²

Number of conductors 4

Electrical data

Operating voltage Ub

Rated current (40 °C)

Environmental conditions

Ambient temperature

-40...85 °C

IP rating

IP68

Material

Conductor insulation material

Housing material

Die-cast zinc, nickel-plated

Housing material, surface protection nickel-plated Material contact carrier

Material contacts

PA Brass

Mechanical data

Lead length L Mounting part 0.50 m M16x1.5

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece. Nut M16 included in scope of delivery

4.0 A

Order Code: BCC099A

Connector Drawings



PIN 1: brown PIN 2: white PIN 3: blue PIN 4: black

Wiring Diagrams