

PRO Multi Material Circular Saw Blade

PRO



- ▶ For cutting various materials, eg non-ferrous metals and plastic materials when installing window frames
- ▶ Highly efficient for window installers: Long Life
- ▶ Designed for cutting various materials
- ▶ Bore works with or without reduction rings to fit different sizes



PRODUCT PROPERTIES								ORDERING INFORMATION				
Outer diameter mm	Bore size mm	Bore with reduction ring mm	Bore with reduction ring inch	Number of teeth	Width of cut (b1) mm / Base bl. thickness (b2) mm	Max. rotation speed (RPM)	Tooth shape	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
130	20	16	-	42	2/1.4	11,500	HLTCG	C1a	1	1	3165140373777	2 608 641 195
150	20	16	-	42	2/1.4	10,000	HLTCG	C1a	1	1	3165140192910	2 608 640 501
160	20	16	-	42	2.4/1.8	9,500	HLTCG	C1a	1	1	3165140192934	2 608 640 503
165	30	-	-	42	2.4/1.8	9,500	HLTCG	C1a	1	1	3165140193092	2 608 640 519
180	30	20	-	48	2.4/1.8	8,500	HLTCG	C1a	1	1	3165140192972	2 608 640 507
184	16	-	-	48	2.4/1.8	8,000	HLTCG	C1a	1	1	3165140263405	2 608 640 815
184	30	-	-	48	2.4/1.8	8,000	HLTCG	C1a	1	1	3165140192965	2 608 640 506
190	20	16	-	54	2.4/1.8	8,000	HLTCG	C1a	1	1	3165140192989	2 608 640 508
190	30	-	-	54	2.4/1.8	8,000	HLTCG	C1a	1	1	3165140192996	2 608 640 509
200	30	-	-	54	2.4/1.8	7,500	HLTCG	C1a	1	1	3165140193009	2 608 640 510
210	30	-	-	54	2.4/1.8	7,000	HLTCG	C1a	1	1	3165140193016	2 608 640 511
230	30	-	-	64	2.4/1.8	6,500	HLTCG	C1a	1	1	3165140193030	2 608 640 513
235	30	25	-	64	2.4/1.8	6,500	HLTCG	C1a	1	1	3165140193047	2 608 640 514