

T602 - PW3 Holster Work Trousers

Collection: PW3

Range: Workwear

Shell Fabric: Titanmill Plus: 65% Polyester, 35% Cotton

Outer Carton: 14

Product information

Rugged trouser made from Kingsmill polyester/cotton 300g fabric with a modern fit and adjustable leg length. Packed full of features to offer superb function and performance including; top loading pre-shaped knee pad pockets, triple stitched seams, crotch gusset to reduce stress and prevent seam failure and a side leg cargo pocket. Pockets have oxford reinforcement for extra durability.

PW3

Utilising premium fabrics, products are engineered for flexibility across a diverse range of industry and trade end uses and offer exceptional value.

Workwear

Portwest workwear offers a range of designs and features suitable for many end uses. Quality fabrics and construction techniques are used guaranteeing comfort and safety. Tested to withstand the rigours of everyday wear each garment has been carefully designed and manufactured to ensure optimum quality at the best price.

Standards

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)



Features

- Durable polycotton fabric for high performance and maximum wearer comfort
- Reflective piping for increased visibility
- 12 Pockets for ample storage
- Swing away tool pockets
- 2 Side pockets
- 2 back pockets with one open and one featuring a flap
- 1 Thigh pocket with zip closure
- 1 Cargo pocket
- 1 Rule pocket
- 1 Pen pocket
- 1 Spanner pocket

T602 - PW3 Holster Work Trousers

Commodity Code: 6203431100

Test House

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
T602ZBR28	Zoom Grey/Black	65.0	45.0	36.0	0.9600	0.1053	5036108291519	25036108781687
T602ZBR30	Zoom Grey/Black	65.0	45.0	36.0	0.9790	0.1053	5036108290031	25036108780253
T602ZBR32	Zoom Grey/Black	65.0	45.0	36.0	1.0030	0.1053	5036108290048	25036108780260
T602ZBR33	Zoom Grey/Black	65.0	45.0	36.0	1.0800	0.1053	5036108297498	25036108787252
T602ZBR34	Zoom Grey/Black	65.0	45.0	36.0	1.0700	0.1053	5036108290055	25036108780277
T602ZBR36	Zoom Grey/Black	65.0	45.0	36.0	1.0800	0.1053	5036108290062	25036108780284
T602ZBR38	Zoom Grey/Black	65.0	45.0	36.0	1.1300	0.1053	5036108290079	25036108780291
T602ZBR40	Zoom Grey/Black	65.0	45.0	36.0	1.1200	0.1053	5036108290086	25036108780307
T602ZBR41	Zoom Grey/Black	65.0	45.0	36.0	1.1500	0.1053	5036108297504	25036108787269
T602ZBR42	Zoom Grey/Black	65.0	45.0	36.0	1.1600	0.1053	5036108290093	25036108780314
T602ZBR44	Zoom Grey/Black	65.0	45.0	36.0	1.1400	0.1053	5036108291526	25036108781694
T602ZBR46	Zoom Grey/Black	65.0	45.0	36.0	1.1800	0.1053	5036108291533	25036108781700
T602ZBR48	Zoom Grey/Black	65.0	45.0	36.0	1.1800	0.1053	5036108291540	25036108781717