

XCKT2121N12

Limit Switch , Thermoplastic Roller Lever Plunger (ZCE21)



List Price \$96.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Actuation	Horizontal - One Way
Actuator Action	Momentary
Actuator	Thermoplastic Roller Lever Plunger (ZCE21)
Head Type	Top Plunger
Operating Torque/Force	53 Inch-Pounds (6Nm)
Repeat Accuracy	0.1mm (on the tripping points)
Lever Arm Length	38.5mm
Marketing Trade Name	OsiSense
Maximum Actuation Speed	1 m/s
Roller Dimension	14 x 5.5mm
RoHS	Yes
Type	XCKT
Type of Duty	General Duty
Body Type	Compact Modular (ZCT21)
Shock Resistance	50G
Body Material	Plastic
Vibration Resistance	25G
Connection Type	Conduit Entrance (0.5" NPT)
Weight	0.250 lbs (0.115kg)
Contact Configuration	1 N.O./1 N.C.
Contact Operation	Snap Action
Positive Opening	Yes
Terminal Type	Screw Clamp
Ampere Rating	10A
Maximum Voltage Rating	240VAC/250VDC
NEMA Enclosure Rating	NEMA 1/2/4/6/12/13
Degree of Protection	IP66/67
Operating Temperature Range	-13 to 158°F (-25 to 70°C)
Approvals	UL Listed - CSA Certified - CE Marked
Conforming to Standards	CENELEC EN 50047

Shipping and Ordering

Generated: 07/13/2010 16:28:04

Category	22418 - Limit Switches, Medium Duty, Compact, IEC, Type XCKP & XCKT
Discount Schedule	T
GTIN	00785901269564
Package Quantity	1
Weight	0.35 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.