

Technical sheet

PPC1001G

Plastic post - grey - with loaded base-Ø 50 / H 950

This premium monobloc marker post is ideal for easily demarcating access points, whether for temporary or permanent use. Constructed from durable ABS and polypropylene materials, it features a weighted monobloc base filled with concrete. The post has two rings – one with holes and the other with hooks – enabling you to attach chains in four different directions. Additionally, it includes a threaded top for mounting information panels. You can select from a range of colours. Please be aware that chains and information panels are available separately.



Customs code	3926909790
EAN	3321369958007

Color : Grey/Black

Material : ABS

Secondary material : Polypropylene

Specifications :

- Premium barrier post for easily defining an access point, either temporarily or permanently.
- One-piece post.
- Concrete-weighted base.
- Two rings: one with holes and one with a hook.
- One threaded head.

Width (mm)	Height (mm)	Base diameter (mm)	Net weight (kg)
280	950	280 x 280	5,50

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com