



ENGLISH

## Datasheet

# NewRS Yellow, Hookup Wire, 300 V, 100m, RoHS Compliant, UL 1581, UL 758 24 AWG

Stock number: 874-0434



American Wire Gauge	24 AWG
Conductor Material	Tinned Copper
Core Strands	11/0.16 mm
Insulation Material	PVC
Insulation Wall Thickness	0.38mm
Length	100m
Maximum Operating Temperature	+80°C
Number of Strands	11
Outer Diameter	1.43mm
Series	1007
Sheath Colour	Yellow
Size of Strands	0.16 mm
Type	Hookup Wire
Voltage Rating	300 V