



Product data sheet

Power tools for trade & industry

Belt Sander

PRO GBS 750



Faster sanding made comfortable

The most important data

Rated input power	850 W
Belt, length	533 mm
Belt speed	200 – 420 m/min

Part Number 0 601 2C1 070

Technical data

Technical data

Belt, length	533 mm
Belt, length 2	533 mm
Belt, width	75 – 75 mm
Rated input power	850 W
No-load speed	200 – 420 rpm
Weight	3.6 kg
Belt speed	200 – 420 m/min
Packaging dimensions (width x length x height)	140 x 387 x 165 mm
Voltage, electrical	230 V

Noise/vibration information

Sanding solid wood

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Cuts sanding time thanks to outstanding removal rate with 850 W motor system
- Comfortable to use with ergonomic grasping design and well-balanced 3.6 kg weight
- Improved sanding stability thanks to vibration-filtering soft cushion and flat solid plate
- Good sanding quality as the sanding belt stays firmly centered while working
- Keeps workspace clean and protects your lungs too, thanks to the higher dust pick-up rate



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

