



## Notice : **TEKNIT GRIP3/4**

Index : 2

### **GUYARD SAS**

22-24, rue Lucien Rouzet  
Z.A. Villedieu sur Indre/Niherne  
36250 NIERNE FRANCE

### **Intermediate risks – PPE category II**

EN 420 :2003 +A1 :2009 EN 388 :2016  
EN ISO 13997 :1999

### **FEATURES :**

- Gloves with 5 fingers, high-density polyethylene knit, gauge 13.
- Elastic wrist with color overlock indicating size.
- Double nitrile coating on the palm and  $\frac{3}{4}$  of the back.
- Slightly textured outer surface.
- Length: 20 to 26 cm
- **AVAILABLE SIZES :**
- Sizes 6 to 12.

### **USAGE PRECAUTIONS :**

- Wear the gloves on clean, dry hands. It is recommended to conduct a prior test of the gloves, as real usage conditions may differ from type-approval tests.
- Before reusing, check that the gloves do not have defects, holes, tears, or abnormal wear.
- Shelf life: 5 years from the manufacturing date indicated on the glove.

### **SAFETY, COMFORT AND DEXTERITY :**

- Dexterity level 5
- Le gant ne contient pas de substances à des taux tels qu'elles sont connues ou suspectées pour avoir des effets néfastes sur l'hygiène ou la santé de l'utilisateur dans les conditions prévisibles d'utilisations.

### **PACKAGING :**

- In case of unpackaging, a copy of the instruction manual must be included with the smallest packaging.
- Bag of 10 pairs
- Carton of 100 pairs

### **MARKING :**

- The CE marking on this glove signifies compliance with the essential health and safety requirements of European Regulation 2016/425 relating to personal protective equipment (PPE).

EN 420 :2003 +A1 :2009



EN 388 :2016



4 X 4 3 D

### **PERFORMANCES LEVELS :**

EN 388 :2016+A1 :2018

- |                                |     |
|--------------------------------|-----|
| • Abrasion :                   | 4/4 |
| • Cut resistance :             | X/5 |
| • Tear resistance :            | 4/4 |
| • Puncture resistance :        | 3/4 |
| • Cut resistance (ISO 13997) : | D/F |

### **LIMITS OF PROTECTION**

- Do not use for handling objects with a temperature above 50°C.
- Do not use for handling chemicals or liquids.

### **RECOMMENDED USES :**

- Handling of metal sheets and sharp metal parts in oily environments.
- Handling of glass panes.
- Waste collection.

### **CARE AND STORAGE**

- No special maintenance is required. It is recommended to store the products in a place protected from light, cool, dry, and well-ventilated.

### **END OF LIFE**

- The end-of-life disposal must be controlled and comply with European traceability and environmental protection requirements.

EU type certificate issued according with module B of Regulation (EU) 2016/425C T C n° : 0075

The EU declaration of conformity is available at

[www.guyard-sa.com](http://www.guyard-sa.com)