

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

EXACT NFC 12-700

INDUSTRIAL EXACT NFC 12-700



The new EXACT screwdrivers – now with lithium-ion technology!

The most important data

Torque (hard)	2 – 12 Nm
Speed	70 – 700 rpm

Part Number 0 602 494 A04

Technical data

Technical data

Description	Centre grip screwdriver
Torque, from (hard)	2 Nm
Torque, to (hard)	12 Nm
Torque (hard)	2 – 12 Nm
Torque, from (soft)	2 Nm
Torque, to (soft)	12 Nm
Torque (soft)	2 – 12 Nm
Speed, from	70 rpm
Speed, up to	700 rpm
Speed	70 – 700 rpm
Direction of rotation	R/L
Weight	1.3 kg
Comment	Below 50% speed setting eventually lower power
Bit holder	1/4" quick change chuck
Battery	18 V / 2.0 Ah battery
Drive type	Battery
Design	Centre grip
Adjustable speed	+
Brushless motor	+
Other torque range possible	+

Lever/trigger start	+
Connector type	Shut-off clutch

Noise/vibration information

Screwdriving

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

