

PRODUCT-DETAILS

AM50753-MG

AM50753-MG Fuse connector unit 13A, Switched w/flex outlet w/LED - MG



General Information

Extended Product Type	AM50753-MG
Product ID	2CLA630829N1701
EAN	8427238098258
Catalog Description	AM50753-MG Fuse connector unit 13A, Switched w/flex outlet w/LED - MG
Long Description	Rated voltage: 230Vac Rated current: 13A Fuse size: Ø6.3x25mm Fuse breaking capacity: 6kA 264V~ 50Hz Fuse according to BS1362 Status indicator LED

Ordering

EAN	8427238098258
Customs Tariff Number	85369010
Minimum Order Quantity	1 piece

Dimensions

Product Net Depth / Length	0.102 m
Product Net Height	0.062 m

Product Net Width	0.102 m
Product Net Weight	0.187 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 EAN	8427238098258
Package Level 1 Depth / Length	0.102 m
Package Level 1 Height	0.062 m
Package Level 1 Width	0.102 m
Package Level 1 Gross Weight	0.187 kg

Technical

Ambient Air Temperature	Operation -5 ... +35 °C Storage -5 ... +50 °C
Degree of Protection	IP20
Mounting Type	Snap mounting
Width in Number of Modular Spacings	1,5

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	9AKK106930A7740
Declaration of Conformity - CE	No declaration needed
Instructions and Manuals	9AKK106930A7740

Classifications

ETIM 7	EC002705 - Holder for cylindrical fuse
ETIM 8	EC002705 - Holder for cylindrical fuse
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switch Assortments → Flush Mounted Range BS - Niessen → Design Millenium → Flush Mounted Inserts with Cover Plate → LED Light / Light Signal

Low Voltage Products and Systems → Switch Assortments → LED Light / Light Signals → LED Light / Light Signal → LED Light / Light Signal - Flush Mounted → LED Light / Light Signal

