

Features

- *Conductor*
Material: 100% copper wires
- *Jacket Material:*
PVC, Black
- *Cable Length:*
0.5M
- *Easy to install and reliable connection*
- *Color: Black*

RS PRO DC Cables

RS Stock No.: 0707850



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against

demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Current: 3A.

Voltage: 12V.

*Material: 2*0.5mm² copper wire.*

Polarity distinction: brown positive, blue negative.

Connector 1: DC 5.5mm x 2.1mm x 9.5mm male right angle 90 degree.

Connector 2: bare wire with terminal crimped.

*This 90-degree right angle plug can be easily go through the narrow gap, will never bend and damage the power supply cord. This cable is suitable for CCTV security cameras, DVRs, surveillance monitoring systems, LED lights or other 2.1*5.5mm DC power equipment.*

General Specifications

<i>Connector A</i>	<i>Male DC5.5*2.1*9.5mm</i>
<i>Connector A Gender</i>	<i>Male</i>
<i>Connector B</i>	<i>Open, terminal crimped</i>
<i>Connector Style</i>	<i>Plug, right angle</i>
<i>Outer Sheath Material</i>	<i>PVC</i>
<i>Sheath Colour</i>	<i>Brown, blue</i>
<i>Connector Plating</i>	<i>Nickel</i>

Electrical Specifications

<i>Connection</i>	<i>Open end cable</i>
<i>Voltage Rating</i>	<i>12V DC</i>
<i>Maximum Power</i>	<i>3A</i>

Mechanical Specifications

Length	0.5m
Cable Specification	2*0.5mm ² copper wire

Operation Environment Specifications

Operating Temperature	0°C to 70°C
Storage Temperature	0°C to 70°C

Approvals

Standards Met	RoHS, Reach
Declarations	RoHS, Reach

