

Pendant control

46-459.1418

Distribution by
Rs-online<https://www.rs-online.eao.com/component/46-45...>

Your product:



46-459.1418 Pendant control

Loading ...

FRONT

Colour: Yellow

MOUNTING

Mounting cut-out: Ø 22 mm

Mounting type: Panel mounting

ELECTRICAL CHARACTERISTICS

Rated insulation voltage U_i : U_i 300V - U_{imp} 2.5KV (IEC-EN60947-1)

Pollution degree: 3

Protection class: II, according to EN / IEC 61140

MECHANICAL CHARACTERISTICS

Tightening torque: 0.8 ... 1.2 Nm (7.1÷10.6 Lb-in)

Weight: 0.4 kg

AMBIENT CONDITION

IP front protection: IP65, IP66

IK front protection: IK08

Operating temperature: – 35 °C ... + 80 °C

CERTIFICATE

Approbations: CSA, UL

