

WINSLOW ADAPTICs

Data Sheet – Stamped SIMM Socket WS3130APRRC

The WS3130APRRC Series features a plastic latch and uses a phosphor bronze contact plated in 6 microns pure tin over 2.5 microns nickel. Moulding material is Liquid Crystal Polymer rated to UL 94 V-0.



Performance Specifications

Current Rating:	1 Amp. Max.
Contact Resistance:	30mΩ max
Capacitance:	2 pF max
Operating Temperature:	-55°C to +105°C
Insulation Resistance:	10,000 MΩ Min. Initial.
Durability:	40 cycles minimum.

