

458788

Hand Brush, 330 mm, Soft, Grey



Remove flour and fine particles from conveyor belts, food preparation surfaces, tables and equipment with this Hand Brush. Suitable for use with the Vikan Dustpan 5660x.

Technical Data

Item Number	458788
Visible bristle length	50 mm
Material	Polypropylene Polyester Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	15 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	1560 Pcs.
Quantity Per Layer (Pallet)	120 Pcs.
Box Length	380 mm
Box Width	290 mm
Box Height	140 mm
Length/Depth	330 mm
Width	35 mm
Height	110 mm
Gross Weight	0,19 kg
Net Weight	0,17 kg
Cubik metre	0,0013 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705022017535
GTIN-14 Number (Box quantity)	15705028017543
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

3. Do not store the product below 0° Celsius.