

FEATURES

- **Nickel Plated Brass Construction:** Provides enhanced durability and corrosion resistance
- **Hose Barb Connection:** Ensures a secure fit with 10 mm hoses
- **Threaded BSPP Connection:** Compatible with 1/4 inch BSPP threaded fittings for versatile use
- **High Pressure Rating:** Supports up to 100 bar, suitable for high-pressure applications
- **Wide Temperature Range:** Operates effectively up to 300 °C, ideal for extreme conditions

RS PRO 10 mm Hose Barb Hose Connector, 1/4 in BSPP Threaded

RS Stock No: 665-601



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO hose connector is designed to facilitate secure and efficient connections between hoses and threaded fittings. Ideal for high-pressure applications, it ensures reliable performance in demanding environments. The nickel-plated brass construction offers excellent durability and resistance to corrosion, making it suitable for both industrial and commercial use.

General Specifications

Connection Gender A	Male
Connection Gender B	Female
Connection Size A	10 mm
Connection Size B	1/4 in
Connection Standard B	BSPP
Connection Type A	Hose Barb
Connection Type B	Threaded
Maximum Operating Pressure	100 bar
Product Type	Hose Connector
Sub Type	Hose Connector

Mechanical Specifications

Body Material	Nickel Plated Brass
Hose Inside Diameter	10 mm

Operation Environment Specifications

Maximum Operating Temperature	300 °C
-------------------------------	--------

Approvals

Standards/Approvals	PED 2014-68-UE, REACH 1907-2006, RoHS 2011-65-CE
---------------------	--

