

## IN 19 LK 8-140

### Screwdriver bit socket 1/2"

with ball end, for in-hex screws, long pattern

|                       |             |
|-----------------------|-------------|
| Code                  | ETIM        |
| 6165160               | EC002157    |
| EAN                   | UNSPSC      |
| 4010886616512         | 27-11-17-01 |
| Country of origin     | eCl@ss      |
| Germany               | 21-04-04-02 |
| Customs tariff number |             |
| 82079030              |             |



### Article description

- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, gun-metal finish
- Total swivel angle approx. 15-20°

### Article information

|  |                       |                           |                               |
|--|-----------------------|---------------------------|-------------------------------|
| Contents (Qty of pieces)               | 1                     | Standard                  | DIN 3120 - C 12,5<br>ISO 1174 |
| Net weight [kg]                        | 0,116 kg              | Width across flats l [mm] | 8                             |
| Total length [mm]                      | 140 mm                | Backup                    | Ball Catching Cricket         |
| Surface                                | chrome-plated         | Tip length                | 102,0 mm                      |
| Material                               | Chrome-vanadium steel | Insert Ø Actuator         | 22,5 mm                       |
| Drive connector square female [metric] | 12,5 mm               | Total swivel angle        | 15 - 20°                      |
| Drive connector square female [inch]   | 1/2"                  |                           |                               |