



Model: **STEGO** **Protection Class:** **S3 SRC CI ESD**
Article: **RL10376** **EU Regulations:** **EN ISO 20345:2011**

DESCRIPTION

RedLion Safety Shoes, with aluminium AirToe® and Save&Flex PLUS anti-perforation system, designed to guarantee a high comfort of the fit. High, light, with water-repellent upper in Putek PLUS® highly resistant to abrasion, closure with laces and bellows in padded nylon to ensure a prolonged well-being of the foot. These work shoes are able to guarantee comfort and lightness thanks to the sole with the innovative Infinergy® system and to the expanded PU midsole. The multi-functional heel and the compact PU tread provide grip, security and stability of posture. This shoe complies with S3 SRC CI ESD safety standards and is suitable for use in humid environments, transport and logistics, the tertiary sector and services.

UPPER

High abrasion resistant PUTEK® PLUS, water resistant and breathable

LINING

Wingtex® air tunnel

SAFETY TOE CAP

AirToe® Aluminium, with breathable membrane

PIERCE-RESISTANCE

Save & Flex PLUS®, pierce resistant "non metal"

FOOTBED

WOW

INTERSOLE

Consisting of soft E-TPU Infinergy® foam

SOLE

PU compact Antislip, antistatic and oil resistant

FIT

Natural Confort 11 Mondopoint®

SIZE

35-48 (UK: 2-13)

