



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 9

Connector Product Type: **Connector Assembly**

Operating Voltage: **250 VDC**

Connector System: **Wire-to-Board**

Sealable: **No**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Number of Positions	9
Number of Power Positions	0
Number of Signal Positions	9

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Reverse Gender	No
----------------	----



Contact Type	Pin
Contact Current Rating (Max)	7.5 A
Contact Protection	With

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Panel Mount Feature Type	Flange with Threaded Inserts
Mating Alignment Type	Keyed
Mating Retention Type	Threaded Coupling
Mating Alignment	With
Connector Mounting Type	Panel Mount
Mating Retention	With
Panel Mount Feature	With

Housing Features

Housing Color	Black
Housing Material	Thermoplastic
Circular Connector Shell Size	11

Dimensions

Assembly Length	29.26 mm[1.152 in]
-----------------	--------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	None

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	27
Packaging Method	Bag



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2407269-4
CAP, CPC, SIZE 11 RECP & 13 PLUG, YELLOW



TE Part # 1-2407269-1
CAP, CPC, SIZE 11 RECP & 13 PLUG, ORANGE



TE Part # 206485-1
CPC PLUG ASSEMBLY SIZE 11-9



TE Part # 1546347-2
R/A CABLE CLAMP KIT, SZ 11, CPC



TE Part # 207489-1
FLEXIBLE CABLE BOOT, SIZE 11



TE Part # 1-206062-4
CABLE CLAMP KIT #11



TE Part # 206358-6
CABLE CLAMP KIT, BULK PKG



TE Part # 206358-5
CABLE CLAMP ASY, SIZE 11



TE Part # 207490-1
CABLE GRIPPER, SIZE 11



TE Part # 796379-2
R/A STRN RELIEF KIT,SZ 11,CPC




TE Part # 1-2407269-2
CAP, CPC, SIZE 11 RECP & 13 PLUG, BLACK



TE Part # 1-2407269-3
CAP, CPC, SIZE 11 RECP & 13 PLUG, RED



TE Part # 1-206062-7
CABLE CLAMP KIT, BULK PKG



TE Part # 207299-1
PLUG MTG. FLANGE NO 11 CPC

Also in the Series | AMP Circular Plastic Connectors



Circular Power Connectors(423)



Connector Backshells(1)



Connector Caps & Covers(16)



Connector Seals & Cavity Plugs(35)



Connector Strain Relief(60)



Insertion & Extraction Tools(1)

Customers Also Bought



TE Part #1-5103308-0
A/L LOW PRO HDR 50P VERT BLACK



TE Part #1-640456-6
16P MTA100 HDR ASSY F/L SQ STR



TE Part #5650470-5
ASSY,PIN,EUROCARD,TYPE R,LEAD-



TE Part #6-104363-1
12 MTE HDR SRST LATCH .100CL



TE Part #1-207369-1
CPC RECEPT ASSY SIZE 17-28 LF

TE Part #234234-E
M8 FEMALE, A CODE, 4P, 16.25MM SMT

TE Part #3-643814-3
03P MTA100 CONN ASSY POL RIB

TE Part #2337224-1
TACT ULTRA TB 2.6X1.6X0.55 160GF

TE Part #2301826-2
AMPL PLUG HD20, VERT, 9P, B/L,4-40 S/LOC

TE Part #1-1462039-8
IM06DGR=IM RELAY 140mW 12V

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-206852-1_AL.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-206852-1_AL.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-206852-1_AL.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Product Specifications

Connector, Circular Plastic

English

Product Specification

English