

Cable Inspector

Efficient, compact, and reliable – the affordable entry into copper data cabling testing. The Cable Inspector is a professional wiremapper that makes testing and optimizing RJ-45 data cabling remarkably easy.

■ Comprehensive Cable Testing

Tests data outlets and connectors for open circuits, short circuits, miswiring, split pairs, and more to ensure flawless cabling performance.

■ Easy to Use

With just three buttons and an intuitive user interface, it can be operated quickly and easily by any user.

■ Compact and Portable

Weighing only 197 g and with compact dimensions of 126 × 74 × 35 mm, the Cable Inspector fits easily in any pocket, toolbox, or backpack.

■ Cable Tracing (Optional)

With an additional tone probe (sold separately), unidentified or unlabeled cables can be quickly and efficiently located.

■ Outstanding Battery Life

The rechargeable 2600 mAh lithium-ion battery provides up to 40 hours of operation on a single charge. Fully rechargeable via USB-C in just 2 hours.

Technical Specifications	Cable Inspector
Application Range	RJ-45 cable testing
Supported Cable Types	Shielded and unshielded copper cables
Max. Wiring Plan Length	300 m
Battery	3.7 V Li-Ion, 2600 mAh, USB-C rechargeable
Charging Time	2 hours
Battery Runtime	40 hours
Display	2" LCD with backlight
Weight	197 g (including battery)
Dimensions (L x W x H)	126 × 74 × 35 mm
Operating Temperature	1°C to 45°C
Storage Temperature	-15°C to +85°C
Safety Standards	IEC 61010-1, 3rd Edition
Voltage Protection	Up to 60V (in 1V steps)
ESD Protection	2 kV
EMC	EN 61326-1
Scope of Delivery	1 Cable Inspector Cable Tester, 1 Remote Unit, Quick Start Guide Please note: USB-C cable not included for charging – deliberately excluded to conserve resources. Note: The tone probe for cable tracing is sold separately and not included in the package.
Order No.	NP-LAN-INS

Features

HANDY AND ROBUST | TESTS COPPER CABLING | BEST PRICE-PERFORMANCE RATIO

