

PRODUCT-DETAILS

TC118-TB

RIVET-MOUNTED BASE .75X.5IN BLUE NY



General Information

Extended Product Type	TC118-TB
Product ID	7TAG009860R0004
EAN	5414363058090
Catalog Description	RIVET-MOUNTED BASE .75X.5IN BLUE NY
Long Description	Rivet-Mounted Base, Blue Nylon 6.6 for Temperatures up to 85 Degrees Celsius, Length of 19.1mm (0.75 Inches), Width of 12.7mm (0.50 Inches), Height of 15mm (0.59 Inches), Rivet Mounted, #8 Clearance Hole up to 4.4 mm (0.173 Inches)

Ordering

EAN	5414363058090
UPC	786210822624

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	10000 piece
Package Level 2 Width	10.9 in 277 mm
Package Level 2 Height	11.3 in 287 mm
Package Level 2 Depth / Length	13.3 in 338 mm

Additional Information

Brand / Label	Ty-Rap
Color	Blue
Effective Date	19680627
Material	Nylon/Polyamide 6.6
Mounting Type	Push Mount
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	TY-RAP FASTENING
Product Type	Self-Riveting Base
Special Functions	Firmly locks into position when projecting pin is pushed into the mounting hole. Slip tie under base to attach bundle.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC118-TB
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC118-TB
REACH Declaration	9AKK107992A8795
RoHS Information	9AKK107992A8805

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

