

PARATHOM PAR16 35 36° 3.1 W/830 GU10

PARATHOM advanced PAR16 | Dimmable LED reflector lamps PAR16 with retrofit pin base



Areas of application

- Spotighting for accents
- Display cabinets and shop windows
- Retail outlets and exhibition rooms
- Spotighting heat-sensitive objects such as food, plants, etc.
- Outdoor applications only in suitable luminaires
- Directional light sources
- Hospitality
- Shops

Product benefits

- Very low energy consumption
- Extremely long life
- Robust against vibrations
- No UV and near-IR radiation in the light beam
- Professional thermal management
- Efficient generation of white light
- Alternative to line-voltage halogen lamps
- Ideal for economical spotighting

Product features

- Professional LED lamps for line voltage
- Dimmable (with many common dimmers, see also www.ledvance.com/dim)
- Made in Europe
- Base: GU10
- Lifetime: up to 35,000 h
- Mercury-free lamps



Product datasheet

- High color consistency; SDCM: < 5 (PARATHOM PRO)

Technical data

Electrical data

| | |
|--|-------------|
| Rated wattage | 3.10 W |
| Nominal wattage | 3.10 W |
| Nominal voltage | 220...240 V |
| Claimed equiv. conventional lamp power | 35 W |
| Operating frequency | 50...60 Hz |
| Power factor λ | 0.85 |


Photometrical data

| | |
|--------------------------------------|---------------------------|
| Luminous intensity | 565 cd |
| Nominal luminous flux | 230 lm |
| Rated luminous flux | 230 lm |
| Color temperature | 3000 K |
| Color rendering index Ra | ≥ 80 |
| Light color (designation) | Warm White |
| Standard deviation of color matching | ≤ 5 sdc _m |
| Nominal useful luminous flux 90° | 230 lm |
| Rated useful luminous flux 90° | 230 lm |
| Rated peak intensity | 565 cd |

Light technical data

| | |
|------------------------------------|---------|
| Beam angle | 36 ° |
| Warm-up time (60 %) | 1.00 s |
| Starting time | 0.0 s |
| Nominal beam angle | 36 ° |
| Rated beam angle (half peak value) | 36.00 ° |

Dimensions & weight



| | |
|-------------------------|---------|
| Overall length | 55.0 mm |
| Diameter | 51.0 mm |
| Outer bulb | PAR51 |
| Length | 55.0 mm |
| Maximum diameter | 51.0 mm |

Lifespan

| | |
|--|---------|
| Nominal lamp life time | 25000 h |
| Rated lamp life time | 25000 h |
| Number of switching cycles | 100000 |
| Lumen main.fact.at end of nom.life time | 0.70 |

Additional product data

| | |
|--|--|
| Base (standard designation) | GU10 |
| Mercury content | 0.0 mg |
| Mercury-free | Yes |
| Appropriate disposal acc. to WEEE | Yes |
| Product remark | All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value/LED lamps contain several electronic components. Under unfavourable conditions these can lead to acoustic noise. In case of resonance even low noise can cause audible effect. Possible factors influencing this are the installation, the design of the lamp holder and the luminaire (acoustic resonance effect) as well as the dimmer or the transformer (harmonics or electronic resonance) |

Product datasheet

Capabilities

| | |
|----------|-----|
| Dimmable | Yes |
|----------|-----|

Certificates & standards

| | |
|-------------------------|-------------|
| Energy efficiency class | A+ |
| Energy consumption | 4 kWh/1000h |

Country specific categorizations

| | |
|-----------------|----------------------------------|
| ILCOS | DRPAR-3,1/830-220-240-GU10-50/36 |
| Order reference | PPAR16D35363,1W |



Guarantee

Logistical Data

| Product code | Product description | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Volume | Gross weight |
|---------------|--------------------------------------|------------------------------|--------------------------------------|----------------------|--------------|
| 4052899957916 | PARATHOM PAR16 35 36° 3.1 W/830 GU10 | Shipping carton box 10 | 257 mm x 110 mm x 70 mm | 1.98 dm ³ | 595.00 g |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

For dimming conformity see

▶ www.ledvance.com/dim

For further products and actual information concerning LED lamps see

▶ www.ledvance.com/ledlamps

For Guarantee see

Product datasheet

▶ www.ledvance.com/guarantee

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.