

## FEATURES

- **Sintered Bronze Material:** Offers excellent wear resistance and durability, ensuring long service life.
- **1.25 in Inside and Outside Diameter:** Provides a perfect fit for standard applications, simplifying installation.
- **0.13 in Thickness:** Ensures optimal load distribution and stability in compact spaces.
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Capable of handling moderate dynamic loads effectively.
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Suitable for high static loads, enhancing performance reliability.
- **ISO 9001:2008, UKAS 001 Approved:** Meets international quality standards, ensuring consistent performance.

## RS PRO Sintered Bronze Thrust Washer, 1.25 in Diameter

RS Stock No: 594-775



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO Sintered Bronze Thrust Washer is designed to provide reliable support and reduce friction in axial load applications. With a robust construction, it is ideal for use in machinery where space is limited and efficient load distribution is essential.

## General Specifications

Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Thrust Washer
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Washer

## Mechanical Specifications

Inside Diameter	1.25 in
Material	Sintered Bronze
Outside Diameter	1.25 in
Thickness	0.13 in

## Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------