

## Datasheet

# 58 W Fluorescent, Ceiling Light Batten, Single Batten, 230 V ac, 1 Lamp, Anti-corrosive

RS Stock 362-7901



### LED CHARACTERISTICS

Ra	°K	L70/B10	P/U	%	R/Rx	PF	LL/CW
80+	4000	60K	P	>85	R	>0.95	91.0

## Specification

- I Robust and durable extruded aluminium body with die-cast ends finished full polyester, non-yellowing white
- I Body dissipates heat, ensuring long control gear life in higher ambient temperatures
- I High impact-resistant textures, flame retardant polycarbonate cover
- I Tamper-resistant cover screws
- I Removable gear tray, hangs on safety straps for easy maintenance
- I Version for high ambient temperatures to 60oC
- I Complies with M.O.D. JSP482 Chapter 8 Document for 'Category C' areas
- I XL version - Miro aluminium
- XL reflectors focus and direct the light efficiently and effectively
- I Smart versions with intelligent lighting control for use up to 10 metres mounting height
- I LED version fitted with 4000K LEDs



Smart version



LED version PCB board



XL version (cover removed)