

Product Specification PDF

Date	Correct as of 25th Apr 2019
Brand	C.K
Product	T5422
Description	MightyRod PRO Cable Rod Super Set 12m
Barcode	5013969950656
Commodity code	8205598000
Country of origin	TW



Features & Benefits

~ Triple bonded steel connectors for extreme torsion and tensile strength □ glued, indented and crimped ~ 12 meters of 100% splinter-proof rods ~ 4 rod flexibilities for overhead, under floor, tight angled and obstructed runs ~ Super flexible, low friction, Spira-FLEX rod for tight angled access points ~ Glow in the dark phosphorescent GLO rod for guiding a run of rods in low light conditions ~ Super tough □MIGHTY-FIX□ zinc plated steel connectors □ tensile strength in excess of 275kg ~ Accessories: flexi-lead (mini-flex), ring, hook, gender changer, flat bullet, domed bullet, in-line swivel, torch, magnet, chain ~ Total contents: 2 x 1m rods 7 mm Ø / 8 x 1m rods 6 mm Ø / 1 x Rod SpriaFlex 4 mm Ø / 1 x rod GLO 6 mm Ø / 1 x FlexiLead / 1 x Hook / 1 x Flat Bullet / 1 x Domed Bullet / 1 x Magnet / 1 x Ring / 1 x Gender Changer / 1 x In-line Swivel / 1 x Torch / 1 x Chain

Applicable Standards

Health & Safety

None applicable

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	0	20
Width mm	45	45	0	1320
Depth mm	45	45	0	230
Height mm	1300	1300	0	180
Weight	1086	1086	0	22.6
Packaging Information	Card use	0	0	Case
	Card gms	0	0	900
	Plastic use	0	0	-
	Plastic gms	0	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0