

**BOSCH**

Invented for life

Power tools for trade & industry

Product data sheet



Sabre Saw

GSA 1100 E

Optimum visibility in any work situation

The most important data

Rated power input	1.100 W
Cutting depth in wood	230 mm
Saw, stroke length	28 mm



Part number: 0 601 64C 870

from GBP 105,00*

[> More product information](#)** Recommended retail price excluding VAT*

Technical data

Rated power input	1.100 W
Stroke rate at no load	0 – 2.700 spm
Weight	3,6 kg
Saw, stroke length	28 mm
Cutting depth	
Cutting depth in wood	230 mm
Cutting depth in metal profiles and metal pipes	20 mm

Noise/vibration information

Sawing wood	
Vibration emission value ah	18.0 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Power tools for trade & industry**Advantages:**

- Integrated LEDs for a better view of the workpiece
- Powerful 1100 W motor for fast sawing progress
- Metal hook for hanging up the tool during a work break
- SDS for fast and convenient blade changes
- Rubber-coated gear housing for a secure and comfortable grip

**Prices / Scope of delivery**

Part number	0 601 64C 870	0 601 64C 860
Carrying case 2 610 956 923	✓	✓
Metal saw blade S 123 XF 2 608 654 416	✓	✓
Voltage 110 V	-	✓
Voltage 240 V	✓	-
Wood saw blade S 2345 X 2 608 654 403	✓	✓
Price (Recommended retail price excluding VAT)	GBP 105,00	GBP 105,00