

Planer LXT®

DKP181

18V • 82 mm

Powerful brushless planer with remote vacuum start capability

Hand planer for up to 3 mm planing depth and 82 mm planing width. Depth adjustment is easy with the thumbwheel. Removable chute port on left or right side. Handy for example for shortening intermediate doors or narrowing panel and moldings.



LXT **BL** **ADT** **AWS**
MOTOR

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
No load speed	12000 min ⁻¹
Planing Width	82 mm
Chip Thickness (Planing Depth)	0 - 3 mm
Max. Shiplapping Depth	25 mm
AWS ready	✓
Sound Power Level (L _{WA})	95 dB(A)
Sound Pressure Level (L _{pA})	87 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,3 - 3,6 kg
Product Dimensions (L x W x H):	366 x 156 x 166 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion

User benefits

- Easy depth adjustment with the thumbwheel.
- The rubber coating on the handle ensures a firm working grip
- The front of the base has 3 grooves for making chamfers.
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Chip ejection can be directed to either side of the tool
- Battery protection system automatically shuts off power when the battery level is low
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitauk.com



Related products

Optional AC

191C19-9

Blade Gauge Assembly

191C22-0

Guide Assembly

193540-6

Set plate

821551-8

Makpac case (3)



191C20-4
Elbow



191C23-8
Edge Fence



782209-3
Socket Wrench 9



835E27-9
Makpac Type 3 Inner tray (3)



Other

User manual

Parts drawing