

T8 Luxline® Plus

F36W/840

0001510



Range features



PRODUCT OVERVIEW

Light colour	840 Cool White
Technology	Fluorescent
Ordering number	0001510
Energy class	A
Lamp shape	Linear
Lamp finish	Coated
Dimmable	Yes
Cap/Base	G13
Type	T8 Luxline Plus
EAN code	5410288015101
CRI (Ra)	85
Colour temperature (K)	4000
Luminous flux (Rated) (lm)	3350
Efficacy (Rated) 100h (lm/W)	93
Watt (Nominal) (W)	36
Voltage (V)	103

T8 Luxline® Plus

F36W/840

0001510

DATA TABLE

General data

Ordering number	0001510
Technology	Fluorescent
Energy class	A
Average life (Nominal) (h)	20000
Lamp shape	Linear
Lamp finish	Coated
Dimmable	Yes
Cap/Base	G13
Type	T8 Luxline Plus
EAN code	5410288015101
E-number SE	8356604
E-number FI	4940474
Product name	F36W/840
Lamp mercury content (mg)	2.8
Control gear required	Yes
Fixture rating	Open
IEC Reference	IEC 60081
IEC Reference 2	IEC 61195
IEC Reference 3	
Intended purpose	General lighting
Special purpose lamp	No
Transformer required	No
Sales pack quantity	25
Rated survival factor at 2000 h 50Hz	0.99
Rated survival factor at 4000 h 50Hz	0.98
Rated survival factor at 6000 h 50Hz	0.96
Rated survival factor at 8000 h 50Hz	0.94
Rated survival factor at 12000 h 50Hz	0.92
Rated survival factor at 16000 h 50Hz	0.8
Rated survival factor at 20000 h 50Hz	0.5

T8 Luxline® Plus

F36W/840

0001510

Optical data

Light colour	840 Cool White
CRI (Ra)	85
Colour temperature (K)	4000
Luminous flux (Rated) (lm)	3350
Luminous flux (Nominal) at 35° C (lm)	
Luminous flux (Nominal) (lm)	3350
Ambient temperature for maximum luminous flux (° C)	25
Rated lumen maint. factor at 2000 h 50Hz	0.96
Rated lumen maint. factor at 4000 h 50Hz	0.94
Rated lumen maint. factor at 6000 h 50Hz	0.92
Rated lumen maint. factor at 8000 h 50Hz	0.91
Rated lumen maint. factor at 12000 h 50Hz	0.9
Rated lumen maint. factor at 16000 h 50Hz	0.89
Rated lumen maint. factor at 20000 h 50Hz	0.87

Electrical data

kWh per 1000 hours burning time	43
Rated lamp efficacy (lm/W) 100H 50Hz at optimum temp.	93
Efficacy (Rated) 100h (lm/W)	93
Watt (Nominal) (W)	36
Watt (Rated) - High frequency (W)	32
Watt (Rated) (W)	32
Voltage (V)	103
Ignition voltage (V)	0
Current (A)	0.43

Physical data


Weight (kg)	0.16
Length base to base (mm) - A	1199.4
Length base to pin Min-Max - B	1204.1-1206.5
Max overall length (mm) - C	1213.6
Max. Lamp Diameter (mm) - D	26
Diameter (mm)	26
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	121.40 x 2.90 x 2.80
Outer package dimensions (L x W x H) (cm)	124.00 x 15.50 x 15.00

T8 Luxline® Plus



F36W/840

0001510

PHOTOMETRY



TECHNICAL DRAWINGS



ENERGY LABEL

T8 Luxline® Plus

F36W/840

0001510

