

1ft (30cm) DisplayPort 1.4 Cable - 8K 60Hz HDR10 - Ultra HD 4K 120Hz Video - DP 1.4 Cable / Cord - For Monitors/Displays - DisplayPort to DisplayPort Cable - M/M

Product ID: DP14VMM1F



This DisplayPort 1.4 cable connects your DisplayPort laptop or desktop computer to an ultra-high definition 8K monitor, TV, or projector. It supports resolutions up to 8K (7680 4320) at 60Hz.

The DisplayPort monitor cable provides the essential connection to support the next generation of ultra-high definition video.

Full-Featured DisplayPort 1.4

This 8K DisplayPort cable supports all DP 1.4 features:

- High Bit Rate 3 (HBR3) bandwidth of 32.4 Gbps, supporting the latest industry standards
- High Dynamic Range (HDR10) for higher contrast ratio and vivid colors
- Multi-Stream Transport (MST) for daisy-chaining multiple monitors
- Display Stream Compression 1.2 (DSC) for maximum resolution output
- Forward Error Correction to manage data transmission errors
- High-Bandwidth Digital Content Protection (HDCP 2.2) for a secure connection between source and display
- 32 uncompressed digital audio channels

Cable Key Features

Aluminum-mylar foil and braided shielding improve EMI protection

Long-lasting flexible TPE jacket and strain relief (TPE is non-toxic and halogen-free for environmental sustainability)

Flexible Cable with Reliable Latched Connectors

The cable has a slim professional grade 4.6 mm cable OD construction that allows for a flexible and clean installation while maintaining superior reliability.

Connector Key Features

Die-cast aluminum sub-structure shielding improves signal integrity and prevents signal degradation

Corrosion-free, gold-plated connectors ensure premium video quality and enhanced reliability

Tested to withstand 5000+ insertions

8K: Enabling Business Continuity

8K has a resolution of 7680 x 4320 and is also known as 4320p and Ultra High Definition (UHD). Suitable for digital signage and other commercial displays that require the highest available resolution, this cable is backward compatible with 4K and 5K displays, making it the perfect peripheral to start futureproofing your cabling infrastructure.

Comprehensive Product Testing & Expert Technical Support

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre- and post-sales.

Certifications, Reports and Compatibility



Applications

Features

- **HIGH PERFORMANCE:** 1ft (30cm) DisplayPort 1.4 cable supports 8K 60Hz (7680x4320p) and 4K 120Hz (3840x2160p) w/HDR10, MST, 32Ch Audio, and GTC for precise audio channel timing; Up to 32.4Gbps bandwidth
- **DURABLE:** Tested to withstand 5000+ insertions & 300+ bend cycles at 120 angle; Long lasting TPE jacket w/ molded Soft TPE strain relief absorbs stress of frequent bends; TPE is non-toxic, halogen free & RoHS certified for environmental sustainability
- **RELIABLE:** 34 AWG video cable built with internal wire manager to ensure signal integrity; Metal connector sub-structure & Al-Mylar Foil w/Braid (85% coverage) for superior EMI shielding; Gold-plated latching DP connectors prevent accidental disconnection
- **APPLICATIONS:** Ideal for high resolution 8K displays; Up to 120Hz refresh rate at 4K resolution; Suitable for high performance GPUs and AV workstations; Supports MST multi-monitor daisy chains; Connect a DP monitor to a UHD

docking station

- SPECS: 1-foot (0.3-meter); Black; DP 1.4 cable; Supports HBR3, 4:4:4 Chroma Subsampling, DSC 1.2, HDCP 2.2; Latching Gold-Plated Connectors; Al-Mylar Foil w/Braided Shield; Compatible with DP 1.2 & previous versions

Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Data Transfer Rate	32.4Gbps
Maximum Digital Resolutions	8K 60Hz (7680 x 4320)
Audio Specifications	DisplayPort - 7.1 Channel Audio DisplayPort - 5.1 Channel Audio

Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DisplayPort (20 pin)

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	0C to 50C (32F to 122F)
Humidity	0%RH ~ 85%RH

Physical Characteristics

Color	Black
Wire Gauge	32 AWG
Cable Length	1.0 ft [0.3 m]

Cable OD	0.2 in [4.6 mm]
Product Length	12.9 in [32.7 cm]
Product Width	0.8 in [2.0 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	1.3 oz [38.0 g]

Packaging Information

Package Length	5.9 in [15.0 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	4.4 oz [126.0 g]

What's in the Box

Included in Package	1 - 1ft Displayport 1.4 8K Cable
---------------------	----------------------------------

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***